
FILTRATION GROUP

ULTRASTAR PHARMA-REPLACEABLE TERMINAL MODULE



CLEANROOM FILTRATION

- Low pressure drop design reduces energy consumption
- Filter retaining system provides easy filter change
- Stainless steel screen (20 gauge with 40% open area) fits flush with housing
- Easy to remove and clean
- Fluid gel sealant ensures a leak free, uniform seal



DESCRIPTION

he Pharma-Replaceable Terminal Module (P-RTM) is designed for applications that require frequent filter testing and routine cleaning procedures as found in hospitals (surgical suites) the pharmaceutical and biotechnology cleanrooms. The P-RTM is easy to install, change filter and provides an optimum service life. A gel seal between the filter and hood eliminates any by-pass leakage. The P-RTM uses 2.0" (51mm) or 4.0" (100mm) mini-pleated media pack with efficiency of 99.99% at 0.3 µm or 99.995% at 0.12 µm particle size. The low profile module is manufactured out of either aluminum or stainless steel. The P-RTM is designed to fit into T-bar ceiling and plaster ceilings. Standard features are collar, diffuser/damper, stainless steel grill and static pressure port. Each unit is subjected to a factory 5-inch positive pressure W.G. leak test. Due to varying end user requirements, custom engineered units are available.

BENEFITS

- An adjustable butterfly damper (range of 30-110 FPM) creates a balanced and uniform airflow resulting in longer service life.
- Lower cost of ownership—only the filter is changed, not the entire unit.
- Rugged leak free construction available in aluminum or stainless steel. Each unit is subject to a factory 5-inch positive pressure W.G. leak test.
- Access to aerosol injection system, test port and damper control for easy service of filter.

APPLICATIONS

The P-RTM is designed to optimize performance in filtration applications for pharmaceutical, biotechnological, medical microelectronics, semiconductors, food processing industries, as well as surgical center operating rooms and isolation areas.





ULTRASTAR PHARMA-REPLACEABLE TERMINAL MODULE

MODULE SIZE*		
ORDER CODE	DESCRIPTION	
P-RTM1	23 5/8 X 23 5/8 (5/8 TRIM FLANGE)	
P-RTM2	23 5/8 X 47 5/8 (5/8 TRIM FLANGE)	
P-RTM3	25 3/8 X 25 3/8 (1 1/2 TRIM FLANGE)	
P-RTM4	25 3/8 X 49 3/8 (1 1/2 TRIM FLANGE)	

Please see price list for order information.

* All dimensions are in inches. Modules are manufactured in 0.063 aluminum (also available in stainless steel), have a perforated 304 SS removable screen with 4 cap-nuts. Filter is not inleuded.

AVAILABLE OPTIONS

- Removable Stainless Steel Trim
- Insulation
- Aerosol Dispersion Nozzle
- Aerosol Dispersion Quick Disconnect
- Seismic Tabs
- Heavy Duty Butterfly Damper
- Guillotine Damper
- Extended Stainless Steel Grill


Please contact us for additional options.

Specifications & drawings available upon request.


FILTERS	
ORDER CODE	DESCRIPTION
*41658	21.62 x 19.88 x 3.5 - 2" MEDIA PACK
*41163	21.62 x 43.88 x 3.5 - 2" MEDIA PACK
*41656	21.62 x 19.88 x 5.25 - 4" MEDIA PACK
*41657	21.62 x 43.88 x 5.25 - 4" MEDIA PACK
-	
**41666	21.62 x 19.88 x 3.5 - 2" MEDIA PACK
**41667	21.62 x 43.88 x 3.5 - 2" MEDIA PACK
**41664	21.62 x 19.88 x 5.25 - 4" MEDIA PACK
**41665	21.62 x 43.88 x 5.25 - 4" MEDIA PACK

^{*} All filters are efficiency 99.99% at 0.3 μm with downstream gel. Downstream screen and divider not included.

TRIM DETAIL



PRESSURE DROP



© FGI 11/04



FILTRATION GROUP

Phone: 877-FGI-TEAM (344-8326) Fax: 800-518-1162

www.filtrationgroup.com e-mail: aerostar@filtrationgroup.com



^{**} All filters are efficiency 99.9995% at 0.12 μm with downstream gel. Downstream screen and divider not included.